

# P300

VACUUM CHAMBER MACHINE



**MULTIVAC**

BETTER PACKAGING



*Optional stainless steel mobile stand available.*

## FEATURING:

- Stainless steel housing.
- Clear acrylic chamber lid.
- Automatic progressive ventilation.
- Double-seam separation sealing.
- Sloped insert and filling plates.
- Function for vacuum quick-stop.
- Three program memory spaces.
- Usable chamber size: 16.5" x 16.5" x 6.7"
- Overall Dimensions: 20.5" x 25" x 15.75" (29.3" open)

DISTRIBUTED EXCLUSIVELY BY



**Processor Division**

5710 NW 41ST STREET • RIVERSIDE MO 64150  
800-456-5624 • [www.bunzlpdpackaging.com](http://www.bunzlpdpackaging.com)

# P300

VACUUM CHAMBER MACHINE  
**MULTIVAC**  
BETTER PACKAGING


## **Clear acrylic chamber lid.**

The complete packaging procedure can be monitored.



## **Double-seam separation sealing.**

P300 seals with a three mm wide primary seal seam and a one mm wide separation seam. The excess film on the pouch can be easily pulled off at the separation seam without using a tool. Also available with gas flushing unit.




## **Automatic progressive ventilation**

When products with sharp edges are being packed, such as pork chops, kebab skewers or salmon portions, the pouch wraps itself gently around the contours of the packed product, reducing the risk of puncturing the pouch.



## **Sloped insert & filling plates**

The sloped insert prevents liquids from flowing out of the pouch during packing. The filling plates reduce the volume of the chamber when smaller or flat products are being packed. The smaller the remaining volume, the shorter the required evacuation time.



## **Three memory spaces for user programs**

The evacuation and sealing times for frequently used applications can be saved on three keys. This includes the gas flushing time in the case of machines with a gas flushing unit.



## **MULTIVAC Hygienic Design™**

The machine is designed for cleaning and disinfection with fluids. Easy-care materials and smooth surfaces ensure quick and simple cleaning. Filling plates, insert and plug-in sealing bar easily removable without tools.



## **Electric**

110V/1P/60Hz/20A or  
220V/3P/60Hz/20A

Cord length: 13' with a 20A plug.



## **SPECIFICATIONS**

ITEM NO.	DESCRIPTION	SEAL BAR LENGTH	CYCLE PER MINUTE	PUMP	ELECTRICAL VOLTS/PHASE/HERTZ/AMPS	GAS	AIR	CASTERS
B529 1202	P300	16.5"	1	1.0 HP	110V1P60HZ20A	N	N	N
B529 1203	P300MAP	16.5"	1	1.0 HP	220V3P60HZ20A	Y	N	N

DISTRIBUTED EXCLUSIVELY BY



**Processor Division**

5710 NW 41ST STREET • RIVERSIDE MO 64150  
800-456-5624 • www.bunzlpdpackaging.com